



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F96T12CWHOCOLD 110W T12 96" Cool White Cold Temp Ho 60 Cri R17D

Sylvania-Ledvance

Catalog Number	F96T12CWHOCOLD
Manufacturer	Sylvania-Ledvance
Description	110W, 96" Mol, T12, Ho (800 Ma), Rapid Start Fluorescent Lamp, Coolwhite Phosphor, 4200K Color Temperature, 60 Cri, Labeled For Cold Temperature Applications.
Weight per unit	1.4 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Recessed Double Contact
bulb type	T12
lumens	8600 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	110

Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200

Descriptions

Description	110W T12 96" COOL WHITE COLD TEMP HO 60 CRI R17D
extra long description	SYL F96T12CWHOCOLDTEMP/25134 F96T12
Long Description	110W, 96" MOL, T12, HO (800 mA), rapid start fluorescent lamp, CoolWhite phosphor, 4200K color temperature, 60 CRI, labeled for cold temperature applications.
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251344
Manufacturers Part Number	F96T12/CW/HO/COLD-TEMP/25134
UPC	046135251344

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	15
Weight Per each	1.41



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial/Residential