



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F96T12CWX 75W T12 96" 4100K CW 87 Cri *Sylvania-Ledvance*

Catalog Number	F96T12CWX
Manufacturer	Sylvania-Ledvance
Description	75W, 96 Inch Mol, T12 Instant Start Slimline Fluorescent Lamp, Deluxe Cool White Phosphor, 4100K Color Temperature, 87 Cri. Vivid Color: High Cri Lamps For Color Critical Applications.
Weight per unit	1.4 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
Base	Single Pin
Lamp Type	INSTANT START
lumens	4400 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	75

### Material, Color, and Finish

color rendering index (cri)	87
color temperature	4100

### Descriptions

Description	75W T12 96" 4100K CW 87 CRI
extra long description	SYL F96T12CWX/29478 F96T12CWX 15/CS
Long Description	75W, 96 inch MOL, T12 instant start Slimline fluorescent lamp, Deluxe Cool White phosphor, 4100K color temperature, 87 CRI. VIVID Color: High CRI lamps for color critical applications.
Special Features	COOL WHITE

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135294785
Manufacturers Part Number	F96T12/CWX/29478
UPC	046135294785

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	15
Weight Per each	1.4333

## Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------