



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F96T12DX 75W T12 96" Daylight Deluxe Single Pin Lamp

Sylvania-Ledvance

Catalog Number	F96T12DX
Manufacturer	Sylvania-Ledvance
Description	75W, 96" Mol, T12 Instant Start Slimline Fluorescent Lamp, Daylight Deluxe Phosphor, 6500K Color Temperature, 88 Cri. Vivid Color: High Cri Lamps For Color Critical Applications.
Weight per unit	1.4 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Single Pin
bulb type	T12
Lamp Type	INSTANT START
lumens	4360 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	75

Material, Color, and Finish

color rendering index (cri)	88
color temperature	6500

Descriptions

Description	75W T12 96" DAYLIGHT DELUXE SINGLE PIN LAMP
extra long description	SYL F96T12DX/29500 F96T12DX 15/CS 1
Long Description	75W, 96" MOL, T12 instant start Slimline fluorescent lamp, Daylight Deluxe phosphor, 6500K color temperature, 88 CRI. VIVID Color: High CRI lamps for color critical applications.

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135295003
Manufacturers Part Number	F96T12/DX/29500
UPC	046135295003



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	15
Weight Per each	1.4333

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------