



## TAMPER-RESISTANT FLOOR BOX ASSEMBLY - ONE GANG FOR WOOD SUB-FLOOR

FB1TRSRN | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Tamper-Resistant Floor Box Assembly, Single Threaded screw plug. Includes 15 amp 125 volt tamper-resistant single receptacle. Nickel.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Tamper-Resistant shutters let plugs in, keep other things out.
- Rugged diecast cover plates.
- Meets UL514(c) and NEC 314.27(c).
- Scrub water compliant.
- With durable nickel or brass cover plates.
- Dual-voltage models available.
- Swing brackets mounting option eliminates drilling tile flooring for mounting screws.
- Wood sub-floors only.
- Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.

---

### SPECIFICATIONS

#### GENERAL INFO

Product Series: Slater

Component Type: Full Assemblies

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121308

UR: No

#### DIMENSIONS

Depth (US): 4

Diameter (US): 6.5"  
Length (US): 4.75  
Width (US): 3.25  
Volume: 20.5

#### TECHNICAL INFORMATION

Material: Nickel  
Floor Type: Wood

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant





## TAMPER-RESISTANT FLOOR BOX ASSEMBLY - ONE GANG FOR WOOD SUB-FLOOR

FB1TRSRN | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Tamper-Resistant Floor Box Assembly, Single Threaded screw plug. Includes 15 amp 125 volt tamper-resistant single receptacle. Nickel.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Tamper-Resistant shutters let plugs in, keep other things out.
- Rugged diecast cover plates.
- Meets UL514(c) and NEC 314.27(c).
- Scrub water compliant.
- With durable nickel or brass cover plates.
- Dual-voltage models available.
- Swing brackets mounting option eliminates drilling tile flooring for mounting screws.
- Wood sub-floors only.
- Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.

---

### SPECIFICATIONS

#### GENERAL INFO

Product Series: Slater

Component Type: Full Assemblies

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121308

UR: No

#### DIMENSIONS

Depth (US): 4

Diameter (US): 6.5"  
Length (US): 4.75  
Width (US): 3.25  
Volume: 20.5

#### TECHNICAL INFORMATION

Material: Nickel  
Floor Type: Wood

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

