



## TAMPER-RESISTANT FLOOR BOX ASSEMBLY - TWO GANG FOR WOOD SUB-FLOORS

FB2TRDR2B | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Tamper-Resistant Floor Box Assembly, Two #8 duplex openings, Four threaded screw plugs. Includes two 3232 15 amp, 125 volt tamper-resistant duplex receptacles. Brass.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Tamper-Resistant shutters let plugs in, keep other things out.
- Rugged diecast cover plates with durable nickel or brass finish.
- Meets UL514(c) and NEC 314.27(c) requirements including scrub water for tile floors.
- Scrub water compliant without caulking, supplied with foam gasket and O-ring-equipped plugs.
- Large box flange rests on finished floor -- no adjustments needed.
- Swing brackets mounting, great for tile floors -- eliminates drilling for mounting screws.
- Extra-deep design leaves plenty of wiring room.

---

### SPECIFICATIONS

#### GENERAL INFO

Product Series: Slater

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121308  
UR: No

#### DIMENSIONS

Depth (US): 4  
Length (US): 4.75  
Width (US): 6.5  
Volume: 42.5

## TECHNICAL INFORMATION

Amps: 15A

Material: Brass, Nickel

Floor Type: Wood

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant





## TAMPER-RESISTANT FLOOR BOX ASSEMBLY - TWO GANG FOR WOOD SUB-FLOORS

FB2TRDR2B | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Tamper-Resistant Floor Box Assembly, Two #8 duplex openings, Four threaded screw plugs. Includes two 3232 15 amp, 125 volt tamper-resistant duplex receptacles. Brass.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Tamper-Resistant shutters let plugs in, keep other things out.
- Rugged diecast cover plates with durable nickel or brass finish.
- Meets UL514(c) and NEC 314.27(c) requirements including scrub water for tile floors.
- Scrub water compliant without caulking, supplied with foam gasket and O-ring-equipped plugs.
- Large box flange rests on finished floor -- no adjustments needed.
- Swing brackets mounting, great for tile floors -- eliminates drilling for mounting screws.
- Extra-deep design leaves plenty of wiring room.

---

### SPECIFICATIONS

#### GENERAL INFO

Product Series: Slater

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121308  
UR: No

#### DIMENSIONS

Depth (US): 4  
Length (US): 4.75  
Width (US): 6.5  
Volume: 42.5

## TECHNICAL INFORMATION

Amps: 15A

Material: Brass, Nickel

Floor Type: Wood

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

