



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street  
72758-6430, AR Rogers  
Phone: 479-636-4190  
Fax: 479-636-5604

## FB40CW6 40W T12 U Bent RS/PH FLR LMP 41K 6" Leg Spacing

*Sylvania-Ledvance*

Catalog Number	FB40CW6
Manufacturer	Sylvania-Ledvance
Description	40W T12, Curvalume Rapid Start Fluorescent Lamp, 6" Leg Spacing, Rare Earth Phosphor, 4100K CCT, 87 Cri. Vivid Color: High Cri For Color Critical Applications.
Weight per unit	0.9500 (lbs/each)
Product Category	Shape Lamps

### Features

amperage rating	Ballast Dependent
average life	18000
Base	Medium Bipin
bulb type	T12
lumens	2,300;2300
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage	100.00 V
Voltage Rating	Ballast Dependent
Wattage	40

### Material, Color, and Finish

color rendering index (cri)	87
-----------------------------	----

### Dimensions and Weight

Diameter	1.5 in
----------	--------

### Descriptions

Description	40W T12 U BENT RS/PH FLR LMP 41K 6" LEG SPACING
extra long description	SYL FB40/CWX/6/24004 FB40CW6 12/C5
Long Description	40W T12, CURVALUME rapid start fluorescent lamp, 6" leg spacing, Rare Earth phosphor, 4100K CCT, 87 CRI. VIVID Color: High CRI for color critical applications.

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135240041
Manufacturers Part Number	FB40/CWX/6/24004
UPC	046135240041

### Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	FLUORESCENT



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street  
72758-6430, AR Rogers  
Phone: 479-636-4190  
Fax: 479-636-5604

## Packaging

Carton	1
Package	12
Weight Per each	0.95