

# Eaton FH28

Catalog Number: FH28

Eaton A200/B100 heater, Used with Starter Sizes 0,1, and 2, A200/B100 Heater, NEMA, Ambient 2.84-3.11, 3.29-3.60A, Non-Comp 2.64-2.89, 3.22-3.53A, Used with Starter Sizes 0,1, and 2, Type A and B, Thermal and Fast Trip

## General specifications



Photo is representative

### Product Name

Eaton A200/B100 heater

### Catalog Number

FH28

### UPC

782114166963

### Product Length/Depth

2.1 in

### Product Height

0.8 in

### Product Width

1.3 in

### Product Weight

0.02 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed  
CSA Certified

### Catalog Notes

Select heater coils based on full load current (FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters

Special features

Used with Starter Sizes 0,1, and 2

Type

A200/B100 Heater

Used with

Used with Starter Sizes 0,1, and 2

Design

NEMA

Full load current range

Ambient 2.84-3.11, 3.29-3.60 A, Non-Comp 2.64-2.89, 3.22-3.53  
A

Overload relay

Type A and B

Trip type

Thermal and fast trip

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Installation instructions

[Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)

Specifications and datasheets

[Eaton Specification Sheet - FH28](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)