

# Eaton FH51

Catalog Number: FH51

Eaton A200/B100 heater, Used with Starter Sizes 1, and 2, A200/B100 Heater, NEMA, Ambient 24.0-26.2, 27.7-30.3A, Non-Comp 22.3-24.3, 26.3-28.8A, Used with Starter Sizes 1, and 2, Type A and B, Thermal and Fast Trip

## General specifications



**Product Name**  
Eaton A200/B100 heater

**UPC**  
786678670393

**Product Height**  
0.8 in

**Product Weight**  
0.03 lb

**Certifications**  
UL Listed  
CSA Certified

**Catalog Number**  
FH51

**Product Length/Depth**  
2.1 in

**Product Width**  
1.3 in

**Warranty**  
Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Catalog Notes**  
Select heater coils based on full load current(FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters

Special features

Used with Starter Sizes 1, and 2

Type

A200/B100 Heater

Used with

Used with Starter Sizes 1, and 2

Design

NEMA

Full load current range

Ambient 24.0-26.2, 27.7-30.3 A, Non-Comp 22.3-24.3, 26.3-28.8  
A

Overload relay

Type A and B

Trip type

Thermal and fast trip

Catalogs

Eaton's Volume 5—Motor Control and Protection

Installation instructions

Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers

Specifications and datasheets

Eaton Specification Sheet - FH51

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia