





GE  
Lighting


**80893 - FLE16/2/R30XL827**

GE Floodlight Soft White R30 - Facilities; Retail Display; Hospitality; Office; Restaurant

a product of  
**ecomagination**



 High Color Rendering  
cUL Listed  
Energy Savings  
 UL Listed



**GENERAL CHARACTERISTICS**

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	R30
Base	Medium Screw (E26)
Equivalent Wattage	65.0 W
Rated Life	10000.0 hrs
Starting Temperature (MIN)	-15.0 °C
LEED-EB MR Credit	467 picograms Hg per mean lumen hour
Primary Application	Indoor Floodlight;Facilities;Retail Display;Hospitality;Office;Restaurant

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	750.0
Mean Lumens	600.0
Nominal Initial Lumens per Watt	50
Color Temperature	2700.0 K
Color Rendering Index (CRI)	82.0

**ELECTRICAL CHARACTERISTICS**

Wattage	16.0
Input Voltage	120.0 V
Input Current	0.2300 A

**DIMENSIONS**

Maximum Overall Length (MOL)	5.5000 in(139.7 mm)
Nominal Length	5.500 in(139.7 mm)

**PRODUCT INFORMATION**

Product Code	80893
Description	FLE16/2/R30XL827
Standard Package	Case
Standard Package GTIN	10043168808931
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168808934

**CAUTIONS & WARNINGS**

**Warning**

- Risk of Electric Shock
  - Do not open - no user serviceable parts inside.
  - Do not use where directly exposed to water or outdoors without an enclosed fixture.





GE  
Lighting


**80893 - FLE16/2/R30XL827**

GE Floodlight Soft White R30 - Facilities; Retail Display; Hospitality; Office; Restaurant

a product of  
**ecomagination**



 High Color Rendering  
cUL Listed  
Energy Savings  
 UL Listed



**GENERAL CHARACTERISTICS**

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	R30
Base	Medium Screw (E26)
Equivalent Wattage	65.0 W
Rated Life	10000.0 hrs
Starting Temperature (MIN)	-15.0 °C
LEED-EB MR Credit	467 picograms Hg per mean lumen hour
Primary Application	Indoor Floodlight;Facilities;Retail Display;Hospitality;Office;Restaurant

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	750.0
Mean Lumens	600.0
Nominal Initial Lumens per Watt	50
Color Temperature	2700.0 K
Color Rendering Index (CRI)	82.0

**ELECTRICAL CHARACTERISTICS**

Wattage	16.0
Input Voltage	120.0 V
Input Current	0.2300 A

**DIMENSIONS**

Maximum Overall Length (MOL)	5.5000 in(139.7 mm)
Nominal Length	5.500 in(139.7 mm)

**PRODUCT INFORMATION**

Product Code	80893
Description	FLE16/2/R30XL827
Standard Package	Case
Standard Package GTIN	10043168808931
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168808934

**CAUTIONS & WARNINGS**

**Warning**

- Risk of Electric Shock
  - Do not open - no user serviceable parts inside.
  - Do not use where directly exposed to water or outdoors without an enclosed fixture.