



GE
Lighting

94547 - GE CFL 23w T3 Spiral

FLE23HT3/2/827

GENERAL CHARACTERISTICS

Base Type	Screw-In
Life in Years	9.1 yr
Rated Life Hours-nominal	10000 h
Base Description	Medium Screw
Product Technology	Compact Fluorescent
Base	E26
Bulb Shape	T3

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	70
Initial Lumens-nominal	1600 lm
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	94547
Description	FLE23HT3/2/827
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168945479
Standard Package GTIN	00043168945479
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168945479
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Estimated Energy Cost per Year	2.77 \$
Dimming Capability	No
Rated power (Watts)	23 W



GE
Lighting

94547 - GE CFL 23w T3 Spiral

FLE23HT3/2/827

GENERAL CHARACTERISTICS

Base Type	Screw-In
Life in Years	9.1 yr
Rated Life Hours-nominal	10000 h
Base Description	Medium Screw
Product Technology	Compact Fluorescent
Base	E26
Bulb Shape	T3

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	70
Initial Lumens-nominal	1600 lm
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	94547
Description	FLE23HT3/2/827
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168945479
Standard Package GTIN	00043168945479
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168945479
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Estimated Energy Cost per Year	2.77 \$
Dimming Capability	No
Rated power (Watts)	23 W