



GE  
Lighting

### 15836 - FLE26HT3/2/827


GE Soft White Spiral® T3 - Facilities; Retail Display; Hospitality; Office; Restaurant

- Up to 75% energy savings One piece unit screws directly into incandescent sockets T3 Spirals® lamps provide economical solution with small overall size
- Long life -8000-12,000 hour rating

a product of  
**ecomagination**



- High Color Rendering
- cUL Listed
- Energy Savings
- UL Listed



#### CAUTIONS & WARNINGS

##### Caution

- Lamp may shatter and cause injury if broken
  - Remove and install by grasping only plastic portion of the lamp.

##### Warning

- Risk of Electric Shock
  - Do not open - no user serviceable parts inside.
  - Do not use where directly exposed to water.

#### NOTES

- Best performance if operated base up and at 77 degrees F (25C) ambient temperature.
- Fluorescent lamp lumens decline during life
- Lumens on one piece self ballasted lamp systems are measured base up.
- Most one piece self ballasted lamps for incandescent sockets and plug-in lamps with screw-in adapters do not work with clip-on shades
- Use only on 120V 60 Hz circuits. Do not use on dimming circuits, photocells or timers. Do not use in wet locations.

#### GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	T3
Base	Medium Screw (E26)
Equivalent Wattage	100.0 W
Rated Life	10000.0 hrs
Starting Temperature (MIN)	-15.0 °C
Total Harmonic Distortion (THD)	120.0 %
LEED-EB MR Credit	313 picograms Hg per mean lumen hour
Primary Application	Standard;Facilities;Retail Display;Hospitality;Office;Restaurant

#### PHOTOMETRIC CHARACTERISTICS

Initial Lumens	1750.0
Mean Lumens	1400.0
Nominal Initial Lumens per Watt	67
Color Temperature	2700.0 K
Color Rendering Index (CRI)	82.0

#### ELECTRICAL CHARACTERISTICS

Wattage	26.0
Voltage	120.0
Input Voltage	120.0 V
Input Current	0.3900 A
Power Factor	0.6

#### DIMENSIONS

Maximum Overall Length (MOL)	5.2000 in(132.1 mm)
Nominal Length	5.100 in(129.5 mm)

#### PRODUCT INFORMATION

Product Code	15836
Description	FLE26HT3/2/827
Standard Package	Case
Standard Package GTIN	10043168158364
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168158367



GE  
Lighting

### 15836 - FLE26HT3/2/827


GE Soft White Spiral® T3 - Facilities; Retail Display; Hospitality; Office; Restaurant

- Up to 75% energy savings One piece unit screws directly into incandescent sockets T3 Spirals® lamps provide economical solution with small overall size
- Long life -8000-12,000 hour rating

a product of  
**ecomagination**



- High Color Rendering
- cUL Listed
- Energy Savings
- UL Listed



#### CAUTIONS & WARNINGS

##### Caution

- Lamp may shatter and cause injury if broken
  - Remove and install by grasping only plastic portion of the lamp.

##### Warning

- Risk of Electric Shock
  - Do not open - no user serviceable parts inside.
  - Do not use where directly exposed to water.

#### NOTES

- Best performance if operated base up and at 77 degrees F (25C) ambient temperature.
- Fluorescent lamp lumens decline during life
- Lumens on one piece self ballasted lamp systems are measured base up.
- Most one piece self ballasted lamps for incandescent sockets and plug-in lamps with screw-in adapters do not work with clip-on shades
- Use only on 120V 60 Hz circuits. Do not use on dimming circuits, photocells or timers. Do not use in wet locations.

#### GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	T3
Base	Medium Screw (E26)
Equivalent Wattage	100.0 W
Rated Life	10000.0 hrs
Starting Temperature (MIN)	-15.0 °C
Total Harmonic Distortion (THD)	120.0 %
LEED-EB MR Credit	313 picograms Hg per mean lumen hour
Primary Application	Standard;Facilities;Retail Display;Hospitality;Office;Restaurant

#### PHOTOMETRIC CHARACTERISTICS

Initial Lumens	1750.0
Mean Lumens	1400.0
Nominal Initial Lumens per Watt	67
Color Temperature	2700.0 K
Color Rendering Index (CRI)	82.0

#### ELECTRICAL CHARACTERISTICS

Wattage	26.0
Voltage	120.0
Input Voltage	120.0 V
Input Current	0.3900 A
Power Factor	0.6

#### DIMENSIONS

Maximum Overall Length (MOL)	5.2000 in(132.1 mm)
Nominal Length	5.100 in(129.5 mm)

#### PRODUCT INFORMATION

Product Code	15836
Description	FLE26HT3/2/827
Standard Package	Case
Standard Package GTIN	10043168158364
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168158367