



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FMV13LCYUNV176 FMV Led Floodlight MT

*Crouse-Hinds*

Catalog Number	FMV13LCYUNV176
Manufacturer	Crouse-Hinds
Description	Led Flood Light, Copper Free Aluminum, 100 to 277 V Ac;108 to 250 V DC, 112 W, 400 W (Hid), 70, 13100 LM Brightness (Lumens), 0.42 to 0.94 A, 5000 K, Epoxy Powder Coated, Glass Lens Material, Yoke Mount, +65 °C Operating Temperature, -40 °C Operating Temperature, 150000 H @ 25 °C;>300000 H @ 55 °C Average Life, 5 Yr Warranty, 32.5 LB
Weight per unit	32.5 (lbs/each)
Product Category	Led Floodlights

### Features

amperage rating	1.608000
Fixture Type	FLOOD
lumens	12940
Shape	Rectangular

### Material, Color, and Finish

Color	Cool White
-------	------------

### Descriptions

Description	FMV LED FLOODLIGHT MT
extra long description	CRS-H FMV13LCY/UNV1-76 LED FLOOD CO
Special Features	GUARD, DARK SKY VISOR, AND TWO ENTRIES WITH LIKE CABLE GLANDS

### Manufacturer Information

Brand	Eaton
GTIN	00662276317307
UPC	662276317307

### Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOOD

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Weight Per each	32.5



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Mounting  
standard

YOKE, POLE, WALL

UL 844, 1598A NEMA 4X, IP66