

Eaton FNM-2-8/10

Catalog Number: FNM-2-8/10

Eaton Bussmann series FNM fuse, Time-delay, 2.8 A, Dual, Non-indicating, Ferrule end x ferrule end, 100 AIC at 250 Vac|10 kAIC at 125 Vac, Nickel-plated bronze endcap, Standard, 250 V



General specifications

Product Name	Catalog Number
Eaton Bussmann series FNM fuse	FNM-2-8/10
UPC	Product Length/Depth
051712520232	1.5 in
Product Height	Product Width
0.41 in	0.41 in
Product Weight	Warranty
0.2 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	

Electrical rating

Amperage Rating

2.8A

Interrupt rating

10 kAIC at 125 Vac

100 AIC at 250 Vac

Voltage rating

250 V

Physical details

Material

Nickel-plated bronze endcap

Number of elements

Dual

Packaging type

Standard

General information

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Superior overload and cycling capabilities

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FNM-2-8/10

Technical data sheets

FNM-2-8/10~FNM-2-8-10~BUSS MIDGET FUSE



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)