

Eaton FNM-3

Catalog Number: FNM-3

Eaton Bussmann series FNM fuse, Time-delay, 3 A, Dual, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 125 Vac|100 AIC at 250 Vac, Nickel-plated bronze endcap, Standard, 250 V

General specifications

Product Name	Catalog Number
Eaton Bussmann series FNM fuse	FNM-3
UPC	EAN
051712520300	5027590449496
Product Length/Depth	Product Height
0.39 in	1.44 in
Product Width	Product Weight
0.39 in	0.2 lb
Warranty	Compliances
Not Applicable	CE Marked RoHS Compliant



Electrical rating

Amperage Rating

3 A

Interrupt rating

10 kAIC at 125 Vac

100 AIC at 250 Vac

Voltage rating

250 V

Physical details

Material

Nickel-plated bronze endcap

Number of elements

Dual

Packaging type

Standard

General information

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Superior overload and cycling capabilities

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FNM-3

Technical data sheets

FNM-3-BUSS MIDGET FUSE

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)