

Eaton FNM-5

Catalog Number: FNM-5

Eaton Bussmann series FNM fuse, Time-delay, 5 A, Dual, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 125 Vac|200 AIC at 250 Vac, Nickel-plated bronze endcap, Standard, 250 V

General specifications

Product Name	Catalog Number
Eaton Bussmann series FNM fuse	FNM-5
UPC	Product Length/Depth
051712520508	1.5 in
Product Height	Product Width
0.41 in	0.41 in
Product Weight	Warranty
0.2 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	



Electrical rating

Amperage Rating

5 A

Interrupt rating

10 kAIC at 125 Vac

200 AIC at 250 Vac

Voltage rating

250 V

Physical details

Material

Nickel-plated bronze endcap

Number of elements

Dual

Packaging type

Standard

General information

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Superior overload and cycling capabilities

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FNM-5

Technical data sheets

FNM-5~BUSS MIDGET FUSE

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)