


# Eaton FNQ-20

Catalog Number: FNQ-20

Eaton Bussmann series FNQ fuse, Time-delay, Motor control transformers, Circuits with in-rush currents, 20 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 500 Vac, Nickel-plated bronze endcap, Standard, 500 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series FNQ fuse	FNQ-20
<b>UPC</b>	<b>EAN</b>
051712786355	5027590060493
<b>Product Length/Depth</b>	<b>Product Height</b>
0.41 in	1.5 in
<b>Product Width</b>	<b>Product Weight</b>
0.41 in	0.175 lb
<b>Warranty</b>	<b>Compliances</b>
Not Applicable	CE Marked RoHS Compliant

## Electrical rating

### Amperage Rating

20 A

### Interrupt rating

10 kAIC at 500 Vac

### Voltage rating

500 V

## Physical details

### Material

Nickel-plated bronze endcap

### Packaging type

Standard

## General information

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Special features

Non-indicating

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - FNQ-20](#)

### Technical data sheets

[FNQ-20~BUSS MIDGET FUSE](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)