

Eaton FNQ-R-1-1/4

Catalog Number: FNQ-R-1-1/4

Eaton Bussmann series FNQ-R fuse, 1.25 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V



General specifications

Product Name	Catalog Number
Eaton Bussmann series FNQ-R fuse	FNQ-R-1-1/4
UPC	EAN
051712496940	5027590407540
Product Length/Depth	Product Height
0.41 in	1.5 in
Product Width	Product Weight
0.41 in	0.15 lb
Warranty	Compliances
Not Applicable	CE Marked
	RoHS Compliant

Electrical Ratings

Amperage Rating

1.25 A

Voltage rating

600 V

General Information

Application

Line protection, small control transformers, industrial control, branch circuits

Connection

Ferrule end x ferrule end

Special features

Rejection style

Physical Details

Type

Current-limiting high inrush time-delay fuse

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FNQ-R-1-1/4](#)

Technical data sheets

[FNQ-R-1-1/4-FNQ-R-1-1-4-CLASS CC TIME DELAY](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)