

# Eaton FNQ-R-2

Catalog Number: FNQ-R-2

Eaton Bussmann series FNQ-R fuse, 2 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series FNQ-R fuse	FNQ-R-2
<b>UPC</b>	<b>EAN</b>
051712147064	5027590060332
<b>Product Length/Depth</b>	<b>Product Height</b>
0.41 in	1.5 in
<b>Product Width</b>	<b>Product Weight</b>
0.41 in	0.15 lb
<b>Warranty</b>	<b>Compliances</b>
Not Applicable	CE Marked RoHS Compliant

## Electrical Ratings

### Amperage Rating

2 A

### Voltage rating

600 V

## General Information

### Application

Line protection, small control transformers, industrial control, branch circuits

### Connection

Ferrule end x ferrule end

### Special features

Rejection style

## Physical Details

### Type

Current-limiting high inrush time-delay fuse

## Resources

### Catalogs

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

[Bussmann series complete full line catalog no. 1007](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - FNQ-R-2](#)

### Technical data sheets

[FNQ-R-2~CLASS CC TIME DELAY](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)