



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FP0.188BK48"S Thin-Wall Heat Shrink Tubing, 3/16 - 48" , BK *Minnesota Mining (3M)*

Catalog Number	FP0.188BK48"S
Manufacturer	Minnesota Mining (3M)
Description	Heat Shrink Tubing, Heat Type; Polyolefin Material; Black Color; 48 Inch; 0.187 Inch Min. Expanded Diameter; 0.093 Inch Max. Recovered Diameter; Ul, Csa Approval; 600 Volt Voltage Rating; 0.02 Inch Thickness; -67 to 275 Deg C Temperature Rating
Weight per unit	N/A
Product Category	Splicing & Terminating Kits

Features

Material	Polyolefin
Maximum Recovered Diameter	0.093 INCH
Minimum Expanded Diameter	0.187 INCH
Shrink Ratio	2:1
Shrink Temperature	100 Deg C
Voltage Rating	600 Volt
Wall Type	THIN

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Length	48 INCH
Thickness	0.02 INCH



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	SIZE 3/16 INCH; PACKAGING QUANTITY 25 PIECES PER CASE
Commodity Description	SPLICING & TERMINATING KITS
extra long description	HEAT TYPE; POLYOLEFIN MATERIAL; BLACK COLOR; 48 INCH; 0.187 INCH MIN. EXPANDED DIAMETER; 0.093 INCH MAX. RECOVERED DIAMETER; UL, CSA APPROVAL; 600 VOLT VOLTAGE RATING; 0.02 INCH THICKNESS; -67 TO 275 DEG C TEMPERATURE RATING; 2:1 SHRINK RATIO; THIN WALL TYPE; 100 DEG C SHRINK TEMPERATURE; SIZE 3/16 INCH; PACKAGING QUANTITY 25 PIECES PER CASE; FP-301 MODEL
Long Description	HEAT SHRINK TUBING, HEAT TYPE; POLYOLEFIN MATERIAL; BLACK COLOR; 48 INCH; 0.187 INCH MIN. EXPANDED DIAMETER; 0.093 INCH MAX. RECOVERED DIAMETER; UL, CSA APPROVAL; 600 VOLT VOLTAGE RATING; 0.02 INCH THICKNESS; -67 TO 275 DEG C TEMPERATURE RATING
Product Type	Heat Shrink Tubing

Manufacturer Information

Brand	Minnesota Mining (3M)
GTIN	00051128595701
Manufacturers Part Number	FP0.188BK48"S
Model	FP-301
UPC	051128595701

Taxonomies, Classifications, and Categories

Category Description	HEAT/COLD SHRINK
Type	HEAT

Packaging

Carton	25
Weight Per each	0

Uses, Certifications, and Standards

Approval	UL, CSA
Temperature Rating	-67 to 275 Deg C