



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FP3011448 Thin-Wall Heat Shrink Tubing, 1/4 - 48", BK *Minnesota Mining (3M)*

Catalog Number	FP3011448
Manufacturer	Minnesota Mining (3M)
Description	Heat Shrink Tube, Black Insulation Color, -67 °F Operating Temperature, +275 °F Operating Temperature, 48 In Overall Length, 600 V, 0.07 LB
Weight per unit	0.0659 (lbs/each)
Product Category	Splicing & Terminating Kits

Descriptions

Description	HEAT SHRINK THIN-WALL TUBING 1/4-48"-BLACK-12PC
extra long description	3M 7100007366 3M™ Heat Shrink Thin-
Features	3M™ Heat Shrink Tubing FP-301 is color coded for quick and easy identification of the wire. This split resistant, flame retardant tubing is used as shrink fit, electrical insulation over cable splices or terminations. The high expansion ratio tubing is mechanically tough, easily markable and resists cold flow. It is ideal for lightweight wire harness covering, fire resistant covering, wire marking, wire bundling and component packaging. It withstands temperatures of 67 to 275 degrees F (55 to 135 degrees
Special Features	Flexible, Polyolefin

Manufacturer Information

GTIN	00051128595770
Manufacturers Part Number	FP0.250BK48"S
UPC	051128595770

Taxonomies, Classifications, and Categories

Category Description	HEAT/COLD SHRINK
Type	Single (Thin) Wall

Packaging

Carton	12
Weight Per each	0.0659

Uses, Certifications, and Standards

standard	UL, CSA, ABS
----------	--------------