

Eaton FRN-R-15

Catalog Number: FRN-R-15

Eaton Bussmann series FRN-R fuse, 15 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 8 sec at 500%, 200 kAIC at 250 V|20 kAIC at 125 Vdc, Standard, 250 V, 125 Vdc



General specifications

Product Name	Eaton Bussmann series FRN-R fuse	Catalog Number	FRN-R-15
UPC	051712101745	Product Length/Depth	2 in
Product Height	0.56 in	Product Width	0.56 in
Product Weight	0.5 lb	Warranty	Not Applicable
Compliances	CE Marked		

Electrical rating

Amperage Rating

15 A

Interrupt rating

200 kAIC at 250 Vac

20 kAIC at 125 Vdc

Response time

8 sec at 500%

Voltage rating

250 Vac, 125 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FRN-R-15](#)

Technical data sheets

[FRN-R-15-FUSETRON DUAL-ELEMENT CLASS RK5](#)

Technical service bulletins

[Datasheet - FNQ-30](#)