

Eaton FRN-R-45

Catalog Number: FRN-R-45

Eaton Bussmann series FRN-R fuse, 45 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 10 sec at 500%, 200 kAIC at 250 V|20 kAIC at 125 Vdc, Standard, 250 V, 125 Vdc

General specifications



Product Name	Catalog Number
Eaton Bussmann series FRN-R fuse	FRN-R-45
UPC	Product Length/Depth
051712101790	3 in
Product Height	Product Width
0.81 in	0.81 in
Product Weight	Warranty
3.1 lb	Not Applicable
Compliances	
CE Marked	

Electrical rating

Amperage Rating

45 A

Interrupt rating

200 kAIC at 250 Vac

20 kAIC at 125 Vdc

Response time

10 sec at 500%

Voltage rating

250 Vac, 125 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Catalogs

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FRN-R-45](#)

Technical data sheets

[FRN-R-45~FUSETRON DUAL-ELEMENT CLASS RK5](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)