

Eaton FRS-R-17-1/2

Catalog Number: FRS-R-17-1/2

Eaton Bussmann series FRS-R fuse, 17.5 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 10 sec at 500%, 200 kAIC at 600 V|20 kAIC at 300 Vdc, Standard, 600 V, 300 Vdc



General specifications

Product Name	Catalog Number
Eaton Bussmann series FRS-R fuse	FRS-R-17-1/2
UPC	Product Length/Depth
051712508315	5 in
Product Height	Product Width
0.81 in	0.81 in
Product Weight	Warranty
0.4 lb	Not Applicable
Compliances	
CE Marked	

Electrical rating

Amperage Rating

17.5 A

Interrupt rating

200 kAIC at 600 Vac

20 kAIC at 300 Vdc

Response time

10 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FRS-R-17-1/2](#)

Technical data sheets

[FRS-R-17-1/2~FRS-R-17-1-2~FUSETRON DUAL ELEMENT FUSE CLASS RK5](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)