

Eaton FRS-R-2-1/4

Catalog Number: FRS-R-2-1/4

Eaton Bussmann series FRS-R fuse, 2.25 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 10 sec at 500%, 200 kAIC at 600 V|20 kAIC at 300 Vdc, Standard, 600 V, 300 Vdc

General specifications

Product Name	Catalog Number
Eaton Bussmann series FRS-R fuse	FRS-R-2-1/4
UPC	EAN
051712508155	5027590426626
Product Length/Depth	Product Height
0.81 in	5 in
Product Width	Product Weight
0.81 in	0.15 lb
Warranty	Compliances
Not Applicable	CE Marked



Electrical rating

Amperage Rating

2.25 A

Interrupt rating

200 kAIC at 600 Vac

20 kAIC at 300 Vdc

Response time

10 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FRS-R-2-1/4

Technical data sheets

FRS-R-2-1/4~FRS-R-2-1-4~FUSETRON DUAL ELEMENT FUSE CLASS
RK5