# Eaton FRS-R-25

# Catalog Number: FRS-R-25

Eaton Bussmann series FRS-R fuse, 25 A, Dual, Class RK5, Nonindicating, Ferrule end x ferrule end, 10 sec at 500%, 20 kAIC at 300 Vdc|200 kAIC at 600 V, Standard, 600 V, 300 Vdc

# General specifications

Product Name Eaton Bussmann series FRS-R fuse

UPC 051712508339

Product Height 2.34 in

Product Weight 2.25 lb

Compliances CE Marked Catalog Number FRS-R-25

Product Length/Depth 11.63 in

Product Width 2.34 in

Warranty

Not Applicable





# Electrical rating

## Amperage Rating

25 A

### Interrupt rating

20 kAIC at 300 Vdc 200 kAIC at 600 Vac

# Response time

10 sec at 500%

## Voltage rating

600 Vac, 300 Vdc

# Physical details

#### Number of elements

Dual

# Packaging type

Standard

# General information

Class

Class RK5

Connection Ferrule end x ferrule end

Fuse indicator

Non-indicating

# Resources

Catalogs Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

Multimedia Bussmann series Fuseology

Specifications and datasheets Eaton Specification Sheet - FRS-R-25

# Technical data sheets FRS-R-25~FUSETRON DUAL ELEMENT FUSE CLASS RK5

#### Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia