

Eaton FRS-R-6-1/4

Catalog Number: FRS-R-6-1/4

Eaton Bussmann series FRS-R fuse, 6.25 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 10 sec at 500%, 200 kAIC at 600 V|20 kAIC at 300 Vdc, Standard, 600 V, 300 Vdc



General specifications

Product Name	Catalog Number
Eaton Bussmann series FRS-R fuse	FRS-R-6-1/4
UPC	Product Length/Depth
051712508247	5 in
Product Height	Product Width
0.81 in	0.81 in
Product Weight	Warranty
0.4 lb	Not Applicable
Compliances	
CE Marked	

Electrical rating

Amperage Rating

6.25A

Interrupt rating

200 kAIC at 600 Vac

20 kAIC at 300 Vdc

Response time

10 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FRS-R-6-1/4](#)

Technical data sheets

[FRS-R-6-1/4~FRS-R-6-1-4~FUSETRON DUAL ELEMENT FUSE CLASS RK5](#)