



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FS1512 12' Fiberglass Advent Stepladder

Louisville Ladder

|                  |   |
|------------------|---|
| Catalog Number   | FS1512  |
| Manufacturer     | Louisville Ladder   |
| Description      | Advent Fiberglass Stepladder, 300 LB Load Rating, 78 In Base Spread, 30-7/8 In Base Width, 137.127 In (Open Height); 145.727 In (Closed Height) Overall Height, 3 In Rung Width, 3 In Step Depth, 11 Steps, 48 LB |
| Weight per unit  | 47.0 (lbs/each)   |
| Product Category | Hand Tools - Ladders  |

### Features

|               |       |
|---------------|-------|
| Load Capacity | 94414 |
|---------------|-------|

### Descriptions

|                  |   |
|------------------|---|
| Description      | 12' FIBERGLASS ADVENT STEPLADDER  |
| Special Features | Features: Protop - Versatile And Durable; Da Boot For Slip Resistant Footing; Inside Spreader Braces; Double-Rivet Step Construction; Wide Back Braces; A Multifunctional Top Designed To Increase Productivity; Hardware TRAY: Recessed Tray Provides Area To Secure Hardware From Falling Off The Top; Paint Bucket Holder: Convenient Recessed Tray Holds Quarter/Half/Full Gallon Paint Buckets; Drill Slots: Two Separate Drill Slots Make For A Variety Of Convenient Options Especially When Also Using The Paint Bucket |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Louisville     |
| GTIN  | 00728865057198 |
| UPC   | 728865057198   |

### Taxonomies, Classifications, and Categories

|                      |         |
|----------------------|---------|
| Category Description | LADDERS |
| Type                 | Type IA |

### Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 47 |

### Uses, Certifications, and Standards

|          |                       |
|----------|-----------------------|
| standard | CSA, ANSI A14.5, OSHA |
|----------|-----------------------|