

# ELECTRICAL ACCESSORIES

## Fluorescent Starters & Wall Plate Inserts

FLUORESCENT STARTERS				
	CATALOG NUMBER	DESCRIPTION	UL	CSA
	<b>FS2</b>	Glow switch starter without reset, 2 pins 14, 15 & 20W.	•	•
	<b>FS4</b>	Glow switch starter without reset, 2 pins 13, 30 & 40W.	•	•
	<b>FS5</b>	Glow switch starter without reset, 2 pins 4, 6 & 8W.	•	•
	<b>FS25</b>	Glow switch starter without reset, 2 pins 22W Circline 25W Std.	•	•
WALL PLATE INSERTS				
DIMENSIONS	CATALOG NUMBER	DESCRIPTION	FINISH	COLOR
	<b>325I</b>	Mounting strap for blank insert. Box mounted.	Polycarbonate	Ivory
	<b>325W</b>	Changes decorator opening to blank.	Plastic	White
	<b>325</b>			Brown
	<b>325BK</b>			Black
	<b>325LA</b>			Light Almond
	<b>325GRY</b>			Grey
	<b>326I</b>	Mounting strap for blank insert. Box mounted.	Painted	Ivory
	<b>326W</b>	Changes decorator opening to blank.	Steel	White
	<b>326</b>			Brown
	<b>326LA</b>			Light Almond
	<b>327I</b>	Mounting strap for dimmer insert. Box mounted.	Painted	Ivory
	<b>327W</b>	Change from decorator to toggle opening.	Steel	White
	<b>327</b>			Brown
	<b>327LA</b>			Light Almond
	<b>80700I</b>	Mounting strap for blank insert. Box mounted.	Thermoset	Ivory
	<b>80700W</b>	Changes toggle opening to blank.	Plastic	White
	<b>80700LA</b>			Light Almond