



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FT40DL841RSECO 40 Watt 4 Pin Compact Fluorescent

Sylvania-Ledvance

| | |
|------------------|---|
| Catalog Number | FT40DL841RSECO |
| Manufacturer | Sylvania-Ledvance |
| Description | Dulux 40W Long Compact Fluorescent Lamp With 4 Pin Base, 4100K Color Temperature, 82 Cri, Ecologic For Use On Magnetic, Electronic and Dimming Ballasts |
| Weight per unit | 0.4000 (lbs/each) |
| Product Category | Integrated Non-Ballasted Lamps |

Features

| | |
|---------------------------|------------------------|
| amperage rating | Ballast Dependent |
| Ballast Type | Electronic and Dimming |
| Base | 2G11 |
| Lamp Type | DULUX L |
| lumens | 3150 |
| Shape | T5 |
| total harmonic distortion | Ballast Dependent |
| Wattage | 40 |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| color rendering index (cri) | 80 - 89 |
|-----------------------------|---------|

Descriptions

| | |
|------------------------|---|
| Description | 40 WATT 4 PIN COMPACT FLUORESCENT |
| extra long description | SYL FT40DL/841/RS/ECO/20586 FT40DL8 |
| Long Description | DULUX 40W long compact fluorescent lamp with 4 pin base, 4100K color temperature, 82 CRI, ECOLOGIC for use on magnetic, electronic and dimming ballasts |

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135205866 |
| Manufacturers Part Number | FT40DL/841/RS/ECO/20586 |
| UPC | 046135205866 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Fluorescent |
| Type | Compact Fluorescent |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.4 |

Uses, Certifications, and Standards

| | |
|----------|---------------------|
| standard | ANSI C78.901 - 2001 |
|----------|---------------------|