



Southwire™

TOOLS & EQUIPMENT

**SIMpull™ NON-CONDUCTIVE
FISH TAPE**

SIMpull™ NON-CONDUCTIVE FISH TAPE

FTSP45-75NCT
FTSP45-125NCT
FTSP3-100NCT
FTSP3-240NCT



**Does not break
when folded**



**Weighs less
than steel**



**Does not
rust**



**Faster install
time**



**Glow in
the dark**



**Non-conductive
leader**



SIMpull™ NON-CONDUCTIVE FISH TAPE

- Spiral extruded polymer design reduces the amount of effort required to push or pull the fish tape through EMT or PVC conduit*
- Non-conductive, glow-in-the-dark, leader allows for easy install over existing wires
- Allows the fish tape to glide through conduit without binding at joints, couplings or 90 degree bends
- Combines the strength of a steel fish tape with greater flexibility than fiberglass fish tapes*

FTSP45-75NCT
FTSP45-125NCT
FTSP3-100NCT
FTSP3-240NCT



| Model # | Stock # | Description | Length |
|---------------|----------|--|-------------|
| FTSP45-75NCT | 63029801 | SIMpull™ Fish Tape 4.5mm 75' Non-Conductive Tip, Large Case | 75ft/22.8M |
| FTSP45-125NCT | 63163701 | SIMpull™ Fish Tape 4.5mm 125' Non-Conductive Tip, Large Case | 125ft/38.1M |
| FTSP3-100NCT | 63029901 | SIMpull™ Fish Tape 3mm 100' Non-Conductive Tip, Medium Case | 100ft/30.4M |
| FTSP3-240NCT | 63029701 | SIMpull™ Fish Tape 3mm 240' Non-Conductive Tip, Large Case | 240ft/73.1M |

* When compared to Southwire™ Steel and Fiberglass fish tapes



Southwire™

TOOLS & EQUIPMENT

**SIMpull™ NON-CONDUCTIVE
FISH TAPE**

SIMpull™ NON-CONDUCTIVE FISH TAPE

FTSP45-75NCT
FTSP45-125NCT
FTSP3-100NCT
FTSP3-240NCT



**Does not break
when folded**



**Weighs less
than steel**



**Does not
rust**



**Faster install
time**



**Glow in
the dark**



**Non-conductive
leader**



SIMpull™ NON-CONDUCTIVE FISH TAPE

- Spiral extruded polymer design reduces the amount of effort required to push or pull the fish tape through EMT or PVC conduit*
- Non-conductive, glow-in-the-dark, leader allows for easy install over existing wires
- Allows the fish tape to glide through conduit without binding at joints, couplings or 90 degree bends
- Combines the strength of a steel fish tape with greater flexibility than fiberglass fish tapes*

FTSP45-75NCT
FTSP45-125NCT
FTSP3-100NCT
FTSP3-240NCT



| Model # | Stock # | Description | Length |
|---------------|----------|--|-------------|
| FTSP45-75NCT | 63029801 | SIMpull™ Fish Tape 4.5mm 75' Non-Conductive Tip, Large Case | 75ft/22.8M |
| FTSP45-125NCT | 63163701 | SIMpull™ Fish Tape 4.5mm 125' Non-Conductive Tip, Large Case | 125ft/38.1M |
| FTSP3-100NCT | 63029901 | SIMpull™ Fish Tape 3mm 100' Non-Conductive Tip, Medium Case | 100ft/30.4M |
| FTSP3-240NCT | 63029701 | SIMpull™ Fish Tape 3mm 240' Non-Conductive Tip, Large Case | 240ft/73.1M |

* When compared to Southwire™ Steel and Fiberglass fish tapes