



**Southwire™**

TOOLS & EQUIPMENT

**SIMpull™ FLEXIBLE METAL  
LEADER FISH TAPE**

**SIMpull™ FLEXIBLE METAL  
LEADER FISH TAPE**

**FTSP45-75FML**

**FTSP45-125FML**

**FTSP3-100FML**

**FTSP3-240FML**

**FTSP45-200FMLT**



**Does not break  
when folded**



**Weighs less  
than steel**



**Does not  
rust**



**Faster install  
time**




**Swiveling  
Leader**



# SIMpull™ FLEXIBLE METAL LEADER FISH TAPE

- Spiral extruded polymer design reduces the amount of effort required to push or pull the fish tape through EMT or PVC conduit\*
- Swiveling flexible metal leader easily glides through bends
- Allows the fish tape to glide through conduit without binding at joints, couplings or 90 degree bends
- Combines the strength of a steel fish tape with greater flexibility than fiberglass fish tapes\*

**FTSP45-75FML**  
**FTSP45-125FML**  
**FTSP3-100FML**  
**FTSP3-240FML**  
**FTSP45-200FMLT**



Model #	Stock #	Description	Length
FTSP45-75FML	59897001	SIMpull™ Fish Tape 4.5mm 75' Flexible Metal Leader, Large Case	75ft/22.8M
FTSP45-125FML	59896901	SIMpull™ Fish Tape 4.5mm 125' Flexible Metal Leader, Large Case	125ft/38.1M
FTSP3-100FML	59897201	SIMpull™ Fish Tape 3mm 100' Flexible Metal Leader, Medium Case	100ft/30.4M
FTSP3-240FML	59897101	SIMpull™ Fish Tape 3mm 240' Flexible Metal Leader, Large Case	240ft/73.1M
FTSP45-200FMLT	63164701	SIMpull™ Fish Tape 4.5mm 200' Flexible Metal Leader, Tube	200ft/60.96M

\* When compared to Southwire™ Steel and Fiberglass fish tapes



**Southwire™**

TOOLS & EQUIPMENT

**SIMpull™ FLEXIBLE METAL  
LEADER FISH TAPE**

**SIMpull™ FLEXIBLE METAL  
LEADER FISH TAPE**

- FTSP45-75FML**
- FTSP45-125FML**
- FTSP3-100FML**
- FTSP3-240FML**
- FTSP45-200FMLT**



**Does not break  
when folded**



**Weighs less  
than steel**



**Does not  
rust**



**Faster install  
time**




**Swiveling  
Leader**



# SIMpull™ FLEXIBLE METAL LEADER FISH TAPE

- Spiral extruded polymer design reduces the amount of effort required to push or pull the fish tape through EMT or PVC conduit\*
- Swiveling flexible metal leader easily glides through bends
- Allows the fish tape to glide through conduit without binding at joints, couplings or 90 degree bends
- Combines the strength of a steel fish tape with greater flexibility than fiberglass fish tapes\*

**FTSP45-75FML**  
**FTSP45-125FML**  
**FTSP3-100FML**  
**FTSP3-240FML**  
**FTSP45-200FMLT**



Model #	Stock #	Description	Length
FTSP45-75FML	59897001	SIMpull™ Fish Tape 4.5mm 75' Flexible Metal Leader, Large Case	75ft/22.8M
FTSP45-125FML	59896901	SIMpull™ Fish Tape 4.5mm 125' Flexible Metal Leader, Large Case	125ft/38.1M
FTSP3-100FML	59897201	SIMpull™ Fish Tape 3mm 100' Flexible Metal Leader, Medium Case	100ft/30.4M
FTSP3-240FML	59897101	SIMpull™ Fish Tape 3mm 240' Flexible Metal Leader, Large Case	240ft/73.1M
FTSP45-200FMLT	63164701	SIMpull™ Fish Tape 4.5mm 200' Flexible Metal Leader, Tube	200ft/60.96M

\* When compared to Southwire™ Steel and Fiberglass fish tapes