



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **GAR1426 4-2/0CU 1/2-3/4ips** *Burndy LLC*

Catalog Number	GAR1426
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 4 Awg (Sol.) - 2/0 Awg (STR.), #7 - #8 Rebar, 7/8" to 1 " Rod, 1/2" - 3/4" Pipe, Bright Dipped.
Weight per unit	0.7100 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Material	Copper
----------	--------

### **Descriptions**

Description	4-2/0CU 1/2-3/4IPS
extra long description	BUR GAR1426 4-2/0CU 1/2-3/4IPS
Long Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), #7 - #8 Rebar, 7/8" to 1 " Rod, 1/2" - 3/4" Pipe, Bright Dipped.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIMUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Wire To Rebar, Fence Post Grounding Connector, Wire To Pipe, Ground Rod Size: 7/8 - 1 IN Outer-Diameter, Tube (ips) Size: 1/2 - 3/

### **Manufacturer Information**

Brand	BURNDY
GTIN	00781810231807
Manufacturers Part Number	GAR1426
UPC	781810231807

### **Taxonomies, Classifications, and Categories**

Category Description	MISC FITTINGS
Type	GAR

### **Packaging**

Carton	1
Package	50
Weight Per each	0.71



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod  
Or Tube Fence Posts, Direct Burial Applications

standard

UL467