



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

GAR1834  
 7818102354099  
 300-500CU 2 IPS  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Width (in) 4.06  
 Length (in) 2.38  
 Height (in) 5.25  
 Size (Hex) or Size (Bolt) 1/2  
 Size (Hex) or Size (Bolt) - in 0.50  
 B Length (in) 2.75  
 Width (Fraction) 4-1/8  
 Height (Fraction) (in) 5-1/4

**General**

Mechanical Grounding Connector,  
 Cable to Rod or Pipe, 300 - 500  
 kcmil, 2" to 2-3/8" Rod, 2" Pipe,  
 Bright Dipped

**Other**

260

**Approvals / Certifications**

Product Description

Type of U Bolt

UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 CULUS  
 Industry Standards  
 Rated for Direct Burial

Y  
 Y  
 Exempt  
 N  
 N  
 UL467  
 Y

**Conductor(s)**

Copper Tube Size (SCH40) - Range  
 Rod Size (Range)  
 Copper Solid Size (Range)  
 Copper Stranded (Range)  
 Rebar Size (Range)

2 IPS IPS  
 2 in-2 3/8 in  
 N/A  
 300 kcmil-500 kcmil  
 N/A

**Physical**

Type of Hardware  
 Installation Torque  
 Type of Plating  
 Plated (Yes or No)  
 Product Material

DURIUM® Silicon Bronze  
 480  
 Bright Dipped  
 N  
 Copper Alloy

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175