



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **GAR2126 2/0AWG Ground Conn** *Burndy LLC*

Catalog Number	GAR2126
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 4 Awg (Sol.) - 2/0 Awg (STR.), 3-1/2" to 4" Rod, 3-1/2" Pipe, Bright Dipped.
Weight per unit	2.0 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Material	COPPER ALLOY
----------	--------------

### **Descriptions**

Description	2/0AWG GROUND CONN
extra long description	BUR GAR2126 4-2/0CU 3 1/2IPS
Long Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 3-1/2" to 4" Rod, 3-1/2" Pipe, Bright Dipped.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIMUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Ground Rod Size: 3-1/2 - 4 IN, Tube (ips) Size: 3-1/2 IN, Installation Torque: 240 IN-LB, Width: 5-3/8 IN, Height: 6-1/4 IN

### **Manufacturer Information**

Brand	BURNDY
GTIN	00781810236802
Manufacturers Part Number	GAR2126
UPC	781810236802

### **Taxonomies, Classifications, and Categories**

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GAR

### **Packaging**

Carton	1
Weight Per each	1.99



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod  
Or Tube, Direct Burial Cable, Fence Post

standard

UL467