



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

GAR6434  
 7818102386088  
 300-500CU 3/8IPS  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Width (in) 2.44  
 Length (in) 2.25  
 Height (in) 3.50  
 Size (Hex) or Size (Bolt) 1/2  
 Size (Hex) or Size (Bolt) - in 0.50  
 B Length (in) 2.00  
 Width (Fraction) 2-1/2  
 Height (Fraction) (in) 3-1/2

**General**

Mechanical Grounding Connector,  
 Cable to Rod or Pipe, 300 kcmil -  
 500 kcmil, 3/8" Pipe, 5/8" - 3/4"  
 Rod, #5-#6 Rebar

Product Description

**Other**

254

**Approvals / Certifications**

Type of U Bolt  
 UL Listed Y  
 CSA Certified Y  
 ROHS Compatible Exempt  
 UL Recognized N  
 CULUS N  
 Industry Standards UL467  
 Rated for Direct Burial Y

**Conductor(s)**

Copper Tube Size (SCH40) - Range 3/8 IPS IPS  
 Rod Size (Range) 5/8 in-3/4 in  
 Copper Solid Size (Range) N/A  
 Copper Stranded (Range) 300 kcmil-500 kcmil  
 Rebar Size (Range) 5 -6

**Physical**

Type of Hardware DURIUM& Silicon Bronze  
 Installation Torque 480  
 Type of Plating Bright Dipped  
 Plated (Yes or No) N  
 Product Material Copper Alloy

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175