











FM7™ Grayloy™ - Iron and Aluminum Unilet® Conduit Bodies with Wedge-Lok™ Clip Covers and Gaskets

For use with Rigid Steel, Rigid Aluminum and IMC Conduit.

These Appleton FM7 conduit bodies, covers and gaskets have the same applications and installation dimensions as Crouse-Hinds Form 7 conduit bodies. Equivalent FM7 and Form 7 items are completely interchangeable.






Appleton FM7 Conduit Bodies NOTE: Refer to page A-15 for Wiring Capacity Tables

| Hub Size (in.) | C  | | LB  | | LL  | | LR  | | T  | |
|----------------|---|----------|--|----------|--|----------|--|----------|---|----------|
| | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum |
| 1/2 | C17 | C17-SA | LB17 | LB17-SA | LL17 | LL17-SA | LR17 | LR17-SA | T17 | T17-SA |
| 3/4 | C27 | C27-SA | LB27 | LB27-SA | LL27 | LL27-SA | LR27 | LR27-SA | T27 | T27-SA |
| 1 | C37 | C37-SA | LB37 | LB37-SA | LL37 | LL37-SA | LR37 | LR37-SA | T37 | T37-SA |
| 1-1/4 | C47 | C47-SA | LB47 | LB47-SA | LL47 | LL47-SA | LR47 | LR47-SA | T47 | T47-SA |
| 1-1/2 | C57 | C57-SA | LB57 | LB57-SA | LL57 | LL57-SA | LR57 | LR57-SA | T57 | T57-SA |
| 2 | C67 | C67-SA | LB67 | LB67-SA | LL67 | LL67-SA | LR67 | LR67-SA | T67 | T67-SA |
| 2-1/2 | C77 | C77-SA | LB77 | LB77-SA | LL77 | LL77-SA | LR77 | LR77-SA | T77 | T77-SA |
| 3 | C87 | C87-SA | LB87 | LB87-SA | LL87 | LL87-SA | LR87 | LR87-SA | T87 | T87-SA |
| 3-1/2 | — | — | LB97 | LB97-SA | LL97 | LL97-SA | LR97 | LR97-SA | T97 | T97-SA |
| 4 | — | — | LB107 | LB107-SA | LL107 | LL107-SA | LR107 | LR107-SA | T107 | T107-SA |

| Hub Size (in.) | E  | | L*  | | TA  | | TB  | | X  | |
|----------------|---|----------|--|----------|--|----------|--|----------|---|----------|
| | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum |
| 1/2 | E17 | E17-SA | L17 | — | TA17 | — | TB17 | TB17-SA | X17 | X17-SA |
| 3/4 | E27 | E27-SA | L27 | — | TA27 | — | TB27 | TB27-SA | X27 | X27-SA |
| 1 | E37 | E37-SA | L37 | — | TA37 | — | TB37 | TB37-SA | X37 | X37-SA |
| 1-1/4 | — | — | L47 | — | TA47 | — | TB47 | TB47-SA | X47 | X47-SA |
| 1-1/2 | — | — | L57 | — | TA57 | — | TB57 | TB57-SA | X57 | X57-SA |
| 2 | — | — | L67 | — | TA67 | — | TB67 | TB67-SA | X67 | X67-SA |

* L Unilets have double opening and are furnished with one steel cover, assembled.

Appleton FM7 Blank Covers and Gaskets (Covers furnished with Stainless Steel Screws)






| FM7 Body Size (in.) | Wedge-Lok Cast Cover  | | Formtite Cast Cover with Integral Gasket  | | Wedge-Lok Stamped Cover  | | Formtite Stamped Cover with Integral Gasket  | | Solid Neoprene Gasket  | |
|---------------------|---|----------|---|----------|--|----------|--|----------|--|---------|
| | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Steel | Aluminum | Steel | Aluminum | | |
| 1/2 | 170F | 170F-SA | 170FG | 170FG-SA | 170 | 170-SA | 170G | 170G-SA | | GASK571 |
| 3/4 | 270F | 270F-SA | 270FG | 270FG-SA | 270 | 270-SA | 270G | 270G-SA | | GASK572 |
| 1 | 370F | 370F-SA | 370FG | 370FG-SA | 370 | 370-SA | 370G | 370G-SA | | GASK573 |
| 1-1/4 | 470F | 470F-SA | 470FG | 470FG-SA | 470 | 470-SA | 470G | 470G-SA | | GASK574 |
| 1-1/2 | 570F | 570F-SA | 570FG | 570FG-SA | 570 | 570-SA | 570G | 570G-SA | | GASK575 |
| 2 | 670F | 670F-SA | 670FG | 670FG-SA | 670 | 670-SA | 670G | 670G-SA | | GASK576 |
| 2-1/2 | 870F | 870F-SA | 870FG | 870FG-SA | 870 | 870-SA | 870G | 870G-SA | | GASK578 |
| 3 | 870F | 870F-SA | 870FG | 870FG-SA | 870 | 870-SA | 870G | 870G-SA | | GASK578 |
| 3-1/2 | 970F | 970F-SA | 970FG | 970FG-SA | 970 | 970-SA | 970G | 970G-SA | | GASK579 |
| 4 | 970F | 970F-SA | 970FG | 970FG-SA | 970 | 970-SA | 970G | 970G-SA | | GASK579 |






FM7™ Grayloy™ - Iron and Aluminum Unilet® Conduit Bodies with Wedge-Lok™ Clip Covers and Gaskets

For use with Rigid Steel, Rigid Aluminum and IMC Conduit.

These Appleton FM7 conduit bodies, covers and gaskets have the same applications and installation dimensions as Crouse-Hinds Form 7 conduit bodies. Equivalent FM7 and Form 7 items are completely interchangeable.






Appleton FM7 Conduit Bodies NOTE: Refer to page A-15 for Wiring Capacity Tables

| Hub Size (in.) | C  | | LB  | | LL  | | LR  | | T  | |
|----------------|---|----------|--|----------|--|----------|--|----------|---|----------|
| | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum |
| 1/2 | C17 | C17-SA | LB17 | LB17-SA | LL17 | LL17-SA | LR17 | LR17-SA | T17 | T17-SA |
| 3/4 | C27 | C27-SA | LB27 | LB27-SA | LL27 | LL27-SA | LR27 | LR27-SA | T27 | T27-SA |
| 1 | C37 | C37-SA | LB37 | LB37-SA | LL37 | LL37-SA | LR37 | LR37-SA | T37 | T37-SA |
| 1-1/4 | C47 | C47-SA | LB47 | LB47-SA | LL47 | LL47-SA | LR47 | LR47-SA | T47 | T47-SA |
| 1-1/2 | C57 | C57-SA | LB57 | LB57-SA | LL57 | LL57-SA | LR57 | LR57-SA | T57 | T57-SA |
| 2 | C67 | C67-SA | LB67 | LB67-SA | LL67 | LL67-SA | LR67 | LR67-SA | T67 | T67-SA |
| 2-1/2 | C77 | C77-SA | LB77 | LB77-SA | LL77 | LL77-SA | LR77 | LR77-SA | T77 | T77-SA |
| 3 | C87 | C87-SA | LB87 | LB87-SA | LL87 | LL87-SA | LR87 | LR87-SA | T87 | T87-SA |
| 3-1/2 | — | — | LB97 | LB97-SA | LL97 | LL97-SA | LR97 | LR97-SA | T97 | T97-SA |
| 4 | — | — | LB107 | LB107-SA | LL107 | LL107-SA | LR107 | LR107-SA | T107 | T107-SA |

| Hub Size (in.) | E  | | L*  | | TA  | | TB  | | X  | |
|----------------|---|----------|--|----------|--|----------|--|----------|---|----------|
| | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum |
| 1/2 | E17 | E17-SA | L17 | — | TA17 | — | TB17 | TB17-SA | X17 | X17-SA |
| 3/4 | E27 | E27-SA | L27 | — | TA27 | — | TB27 | TB27-SA | X27 | X27-SA |
| 1 | E37 | E37-SA | L37 | — | TA37 | — | TB37 | TB37-SA | X37 | X37-SA |
| 1-1/4 | — | — | L47 | — | TA47 | — | TB47 | TB47-SA | X47 | X47-SA |
| 1-1/2 | — | — | L57 | — | TA57 | — | TB57 | TB57-SA | X57 | X57-SA |
| 2 | — | — | L67 | — | TA67 | — | TB67 | TB67-SA | X67 | X67-SA |

* L Unilets have double opening and are furnished with one steel cover, assembled.

Appleton FM7 Blank Covers and Gaskets (Covers furnished with Stainless Steel Screws)

| FM7 Body Size (in.) | Wedge-Lok Cast Cover  | | Formtite Cast Cover with Integral Gasket  | | Wedge-Lok Stamped Cover  | | Formtite Stamped Cover with Integral Gasket  | | Solid Neoprene Gasket  | |
|---------------------|---|----------|---|----------|--|----------|--|----------|--|--|
| | Grayloy-Iron | Aluminum | Grayloy-Iron | Aluminum | Steel | Aluminum | Steel | Aluminum | | |
| 1/2 | 170F | 170F-SA | 170FG | 170FG-SA | 170 | 170-SA | 170G | 170G-SA | GASK571 | |
| 3/4 | 270F | 270F-SA | 270FG | 270FG-SA | 270 | 270-SA | 270G | 270G-SA | GASK572 | |
| 1 | 370F | 370F-SA | 370FG | 370FG-SA | 370 | 370-SA | 370G | 370G-SA | GASK573 | |
| 1-1/4 | 470F | 470F-SA | 470FG | 470FG-SA | 470 | 470-SA | 470G | 470G-SA | GASK574 | |
| 1-1/2 | 570F | 570F-SA | 570FG | 570FG-SA | 570 | 570-SA | 570G | 570G-SA | GASK575 | |
| 2 | 670F | 670F-SA | 670FG | 670FG-SA | 670 | 670-SA | 670G | 670G-SA | GASK576 | |
| 2-1/2 | 870F | 870F-SA | 870FG | 870FG-SA | 870 | 870-SA | 870G | 870G-SA | GASK578 | |
| 3 | 870F | 870F-SA | 870FG | 870FG-SA | 870 | 870-SA | 870G | 870G-SA | GASK578 | |
| 3-1/2 | 970F | 970F-SA | 970FG | 970FG-SA | 970 | 970-SA | 970G | 970G-SA | GASK579 | |
| 4 | 970F | 970F-SA | 970FG | 970FG-SA | 970 | 970-SA | 970G | 970G-SA | GASK579 | |