



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GC2929 Burndy Connector *Burndy LLC*

Catalog Number	GC2929
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, 2 Cables to 1/4" Thick Bar, 2/0 Awg (Sol) -250 Kcmil, 1/2" Stud, Torque:480 LB In.
Weight per unit	0.4900 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
----------	--------

Descriptions

Description	BURNDY CONNECTOR
extra long description	BUR GC2929 2/0-250 CU-BAR (2)2PC GR
Long Description	Mechanical Grounding Connector, 2 Cables to 1/4" Thick Bar, 2/0 AWG (Sol) -250 kcmil, 1/2" Stud,Torque:480 lb in.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Wide Range Of Two Parallel Cables To 1/4 IN Thick Bar, Type GC Separates Cable From Bar, GCM Clamps Cable To Bar Surface, One-Wrench Installation, UL467 Listed, The High Copper Alloy Cast Body And DURIMUM Bolts, Nuts, And Lockwashers Make The GC And GCM Suitable For Direct Burial In Concrete Or Ground, Width: 2-1/4 IN, Installation Torque: 240 IN-LB, Height: 2-1/4 IN, Bar Thickness: 1/4 IN

Manufacturer Information

Brand	BURNDY
GTIN	00781810231722
Manufacturers Part Number	GC2929
UPC	781810231722

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GC

Packaging

Carton	1
Weight Per each	0.49



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Joining A Wide Range Of Two Parallel Copper Cables, Direct
Burial In Concrete Or Ground

standard

UL467