



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GC38 3/8" Flex Conn D/C Screw In *Appleton/Oz Gedney*

Catalog Number	GC38
Manufacturer	Appleton/Oz Gedney
Description	Features:0.38IN Dia X 1.3IN Length, For Flexible Metal Conduit, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:0.375IN, Material:Zinc Die Cast
Weight per unit	0.0500 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

angle	Straight
connection	Male NPS Thread
Connector Type	Screw In
insulation	Non Insulated
Material	Zinc Die Cast

### Material, Color, and Finish

Color	Metallic
Finish	Natural

### Dimensions and Weight

Size	0.375
------	-------

### Descriptions

Description	3/8" FLEX CONN D/C SCREW IN
extra long description	EGS GC-38 3/8 IN SCREW IN CONN
Long Description	Features:0.38IN Dia X 1.3IN Length, For Flexible Metal Conduit, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:0.375IN, Material:Zinc Die Cast
Product Type	3/8 In Screw In Conn
Special Features	0.38 IN Dia X 1.3 IN Length, For Flexible Metal Conduit

### Manufacturer Information

Brand	Appleton
GTIN	00687855203383
Manufacturers Part Number	GC38
UPC	687855203383

### Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	Screw In Connector

### Trade Size

Trade Size	0-50
------------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	50
Package	500
Weight Per each	0.05

## Uses, Certifications, and Standards

Application	Screw-In Connector for flexible metal conduit
environmental conditions	Dry Location
nema rating	FB-1
standard	UL Standard: 514B; UL Listed: E32539, CSA Standard: C22.2 No. 18.3, CSA Certified: 208044; NEMA: FB-1