



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GE432MAXGN 3-4 Lamp F32T8 120/277V Elect Inst Ballast

Ge By Current Lamps

Catalog Number	GE432MAXGN
Manufacturer	Ge By Current Lamps
Description	Ge Ultramax™, 60 HZ, Normal Ballast Factor, Instant Start, 9.5 In Length, 1.3 In Width, 1.18 In Height
Weight per unit	1.3 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

Ballast Factor	Normal
start type	Instant Start

Dimensions and Weight

Height	1.18
Length	9.5
Width	1.3

Descriptions

Description	3-4 LAMP F32T8 120/277V ELECT INST BALLAST
extra long description	GEL GE432MAX-G-N 74463 ELECTRONIC B
Long Description	GE UltraMax™, 60 Hz, Normal Ballast Factor, Instant Start, 9.5 IN Length, 1.3 IN Width, 1.18 IN Height
Product Type	74463 Electronic Ballast
Special Features	GE432MAX-G-N (Replaces GE-432-MV-N) Designation

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168744638
Manufacturers Part Number	GE432MAX-G-N
UPC	043168744638

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Ballasts_Fluorescent_Electronic

Packaging

Carton	1
Package	10
Weight Per each	1.28

Uses, Certifications, and Standards

Frequency Rating	60.0
------------------	------