



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GE432MAXPLULTRA 3-4 F32T8 Inst Start BLST

Ge By Current Lamps

| | |
|------------------|--|
| Catalog Number | GE432MAXPLULTRA |
| Manufacturer | Ge By Current Lamps |
| Description | Fluorescent Ballast, Instant, 32 W, 120 V/277 V, Non Dimmable, 4 Lamps, 9.5 In Length, 1.7 In Width, 1.18 In Height, 0.95;0.84;0.87;0.77;0.77 Ballast Factor, 0.99;0.91;0.94 Power Factor, 50 HZ;60 HZ, 13 % (120 V);19 % (277 V) Total Harmonic Distortion, -22 °F Starting Temperature, 1.40 LB/Ea |
| Weight per unit | 1.3 (lbs/each) |
| Product Category | Electronic Linear Fluorescent |

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | 3-4 F32T8 INST START BLST |
| extra long description | GEL GE432MAXPL/ULTRA 78625 ELECTRON |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168786256 |
| Manufacturers Part Number | GE432MAXPL/ULTRA |
| UPC | 043168786256 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------------|
| Category Description | ELECTRONIC BALLAST |
| Type | Ballasts_Fluorescent_Electronic |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 1.25 |