



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

106 Industrial Drive
71292-0000, LA West Monroe
Phone: 318-398-9757
Fax: 318-398-9704



GE432MAXPLULTRA 3-4 F32T8 Inst Start BLST

Ge By Current Lamps

Catalog Number	GE432MAXPLULTRA
Manufacturer	Ge By Current Lamps
Description	Fluorescent Ballast, Instant, 32 W, 120 V/277 V, Non Dimmable, 4 Lamps, 9.5 In Length, 1.7 In Width, 1.18 In Height, 0.95;0.84;0.87;0.77;0.77 Ballast Factor, 0.99;0.91;0.94 Power Factor, 50 HZ;60 HZ, 13 % (120 V);19 % (277 V) Total Harmonic Distortion, -22 °F Starting Temperature, 1.40 LB/Ea
Weight per unit	1.3 (lbs/each)
Product Category	Electronic Linear Fluorescent

Descriptions

Description	3-4 F32T8 INST START BLST
extra long description	GEL GE432MAXPL/ULTRA 78625 ELECTRON

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168786256
Manufacturers Part Number	GE432MAXPL/ULTRA
UPC	043168786256

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Ballasts_Fluorescent_Electronic

Packaging

Carton	1
Package	10
Weight Per each	1.25