



### Circuit Guard® Bulk Pack GFCI Receptacles

Description	Rating	Color	Catalog Number	
Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple. Bulk packed, (50 pieces without wallplate).	15 and 20A 125V AC	Black	<b>GF15BKLABULK</b>	<b>GF20BKLABULK</b>
		Brown	<b>GF15LABULK</b>	<b>GF20LABULK</b>
		Gray	<b>GF15GYLABULK</b>	<b>GF20GYLABULK</b>
		Ivory	<b>GF15ILABULK</b>	<b>GF20ILABULK</b>
		Light Almond	<b>GF15LALABULK</b>	<b>GF20LALABULK</b>
		Red	<b>GF15RLABULK</b>	<b>GF20RLABULK</b>
		White	<b>GF15WLABULK</b>	<b>GF20WLABULK</b>



GF15BKLABULK



GF20GYLABULK



GFBF20ILA

### Circuit Guard® Faceless GFCI

Description	Rating	Color	Catalog Number	
Faceless, nylon top, back and side wired, multiple drive screws, self-grounding staple.	20A 125V AC	Black	-	<b>GFBF20BKLA</b>
		Brown	-	<b>GFBF20LA</b>
		Gray	-	<b>GFBF20GYLA</b>
		Ivory	-	<b>GFBF20ILA</b>
		Light Almond	-	<b>GFBF20LALA</b>
		Red	-	<b>GFBF20RLA</b>
		White	-	<b>GFBF20WLA</b>

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with a matching color nylon wallplate.

### Combination Switch/GFCI

Description	Rating	Color	Catalog Number	
Single-pole switch, GFCI grounding receptacle, back and side wired, matching nylon wallplate included.	15A 120V (Switch) 15A 125V (Receptacle)	Ivory	<b>GFSP15IC</b>	-
		Light Almond	<b>GFSP15LAC</b>	-
		White	<b>GFSP15WC</b>	-



GFSP15WC

### GFCI Receptacle Specifications per GFCI Products Listed (Pages K-2 to K-9)

Trip Level	4 to 6 mA.
Trip Time	.025 second nominal.
Frequency	60 Hz.
Voltage	120V AC +10% - 15% (102V to 132V).
Amperage	15A/20A, 20A Feed Thru.
Maximum Interrupting Capacity	10,000A.
Operating Temperature	-35°C to 66°C or -30°F to 150°F.
Maximum Humidity	95%.
Listings and Standards	Meets UL498 for receptacles, UL943 Class A for GFCIs UL File E41978. CSA Certified.
Codes	Meets all NEC® and CEC requirements. NEMA WD-6 ANSI 73.

NEC® is a registered trademark of the National Fire Protection Association (NFPA).

**Safety and Economy**



**GF15ILA**

**10kA Short Circuit Current Rating**

- Comprehensive diagnostics
  - When test button is actuated, both the electronic components and mechanical trip mechanism are functionally tested
- Ground fault indicator
  - Flashing **RED** indicates device has lost capability to provide protection
- No power at face if reverse wired
  - Open circuit condition eliminates false assumption of protection at face
- Installation ease
  - Internal back wiring
  - Automatic grounding feature
  - Captive mounting screws



**GF15ILA**







**GFTR20I**



**GFBF20ILA**

**GFCI Duplex Receptacles, Flush Nylon Face, Matching Nylon Wallplate Included**

Description	 Weather and Tamper-Resistant	 15A 125V NEMA 5-15R UL/CSA Standard	 Weather and Tamper-Resistant	 20A 125V NEMA 5-20R UL/CSA Standard
	Termination	Self-Grounding, Back and Side Wire	Self-Grounding, Back and Side Wire	Self-Grounding, Back and Side Wire
Rating	15A 125V AC NEMA 5-15R	15A 125V AC NEMA 5-15R	20A 125V AC NEMA 5-20R	20A 125V AC NEMA 5-20R
Black	<b>GFTR15BK</b>	<b>GF15BKLA</b>	<b>GFTR20BK</b>	<b>GF20BKLA</b>
Brown	<b>GFTR15</b>	<b>GF15LA</b>	<b>GFTR20</b>	<b>GF20LA</b>
Gray	<b>GFTR15GY</b>	<b>GF15GYLA</b>	<b>GFTR20GY</b>	<b>GF20GYLA</b>
Ivory	<b>GFTR15I</b>	<b>GF15ILA</b>	<b>GFTR20I</b>	<b>GF20ILA</b>
Light Almond	<b>GFTR15LA</b>	<b>GF15LALA</b>	<b>GFTR20LA</b>	<b>GF20LALA</b>
Red	<b>GFTR15R</b>	<b>GF15RLA</b>	<b>GFTR20R</b>	<b>GF20RLA</b>
White	<b>GFTR15W</b>	<b>GF15WLA</b>	<b>GFTR20W</b>	<b>GF20WLA</b>

Note: See page Tech-10 for Weather and Tamper-Resistant descriptions.  
 Bulk 50 pack available without plates, add **"BULK"** suffix. Example: **GFTR20WBULK**.

**GFCI Faceless Receptacles, Flush Nylon Face, Matching Nylon Wallplate Included**

Description	Circuit Guard® Faceless
Termination	Self-Grounding, Back and Side Wire
Rating	20A 125V NEMA 5-20R
Black	<b>GFBF20BKLA</b>
Brown	<b>GFBF20LA</b>
Gray	<b>GFBF20GYLA</b>
Ivory	<b>GFBF20ILA</b>
Light Almond	<b>GFBF20LALA</b>
Red	<b>GFBF20RLA</b>
White	<b>GFBF20WLA</b>