

# Eaton GFEP120

Catalog Number: GFEP120

Eaton BR GFCI circuit breaker, Industrial ground fault thermal-magnetic equipment protector, 20 A, 10 kAIC, Single-pole, 120 V, GFEP, Common, #14-4 AWG, Ground fault circuit interrupter, GFI

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR GFCI circuit breaker	GFEP120
<b>UPC</b>	<b>Product Length/Depth</b>
786676382052	3 in
<b>Product Height</b>	<b>Product Width</b>
1.25 in	4.75 in
<b>Product Weight</b>	<b>Warranty</b>
0.45 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 489	Meets Federal Spec Classification W-C375

## Product specifications

### Type

Industrial ground fault thermal-magnetic equipment protector

### Amperage Rating

20 A

### Voltage rating

120 V

### Trip Type

Common

### Circuit protection

Ground fault circuit interrupter

### Indicators

GFI

### Interrupt rating

10 kAIC

### Main circuit breaker

GFEP

### Wire size

#14-4 AWG

### Number of poles

Single-pole

## Resources

### Catalogs

[Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1](#)

### Specifications and datasheets

[Eaton Specification Sheet - GFEP120](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton GFEP120

Catalog Number: GFEP120

Eaton BR GFCI circuit breaker, Industrial ground fault thermal-magnetic equipment protector, 20 A, 10 kAIC, Single-pole, 120 V, GFEP, Common, #14-4 AWG, Ground fault circuit interrupter, GFI

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR GFCI circuit breaker	GFEP120
<b>UPC</b>	<b>Product Length/Depth</b>
786676382052	3 in
<b>Product Height</b>	<b>Product Width</b>
1.25 in	4.75 in
<b>Product Weight</b>	<b>Warranty</b>
0.45 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 489	Meets Federal Spec Classification W-C375

## Product specifications

### Type

Industrial ground fault thermal-magnetic equipment protector

### Amperage Rating

20 A

### Voltage rating

120 V

### Trip Type

Common

### Circuit protection

Ground fault circuit interrupter

### Indicators

GFI

### Interrupt rating

10 kAIC

### Main circuit breaker

GFEP

### Wire size

#14-4 AWG

### Number of poles

Single-pole

## Resources

### Catalogs

[Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1](#)

### Specifications and datasheets

[Eaton Specification Sheet - GFEP120](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)