

Specifications



Photo is representative



Eaton GFEP120

Eaton BR GFCI circuit breaker, Industrial ground fault thermal-magnetic equipment protector, 20 A, 10 kAIC, Single-pole, 120 V, GFEP, Common, #14-4 AWG, Ground fault circuit interrupter, GFI

General specifications

PRODUCT NAME	Eaton BR GFCI circuit breaker
CATALOG NUMBER	GFEP120
UPC	786676382052
PRODUCT LENGTH/DEPTH	3 in
PRODUCT HEIGHT	1.25 in
PRODUCT WIDTH	4.75 in
PRODUCT WEIGHT	0.45 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 489
CATALOG NOTES	Meets Federal Spec Classification W-C375



Powering Business Worldwide

Product specifications

TYPE	Industrial ground fault thermal-magnetic equipment protector
AMPERAGE RATING	20 A
VOLTAGE RATING	120 V
TRIP TYPE	Common
CIRCUIT PROTECTION	Ground fault circuit interrupter
INDICATORS	GFI
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	GFEP
WIRE SIZE	#14-4 AWG
NUMBER OF POLES	Single-pole

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - GFEP120
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton GFEP120

Eaton BR GFCI circuit breaker, Industrial ground fault thermal-magnetic equipment protector, 20 A, 10 kAIC, Single-pole, 120 V, GFEP, Common, #14-4 AWG, Ground fault circuit interrupter, GFI

General specifications

PRODUCT NAME	Eaton BR GFCI circuit breaker
CATALOG NUMBER	GFEP120
UPC	786676382052
PRODUCT LENGTH/DEPTH	3 in
PRODUCT HEIGHT	1.25 in
PRODUCT WIDTH	4.75 in
PRODUCT WEIGHT	0.45 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 489
CATALOG NOTES	Meets Federal Spec Classification W-C375



Powering Business Worldwide

Product specifications

TYPE	Industrial ground fault thermal-magnetic equipment protector
AMPERAGE RATING	20 A
VOLTAGE RATING	120 V
TRIP TYPE	Common
CIRCUIT PROTECTION	Ground fault circuit interrupter
INDICATORS	GFI
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	GFEP
WIRE SIZE	#14-4 AWG
NUMBER OF POLES	Single-pole

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - GFEP120
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

