

# Specifications



Photo is representative



## Eaton GFEP120

Eaton BR GFCI circuit breaker, Industrial ground fault thermal-magnetic equipment protector, 20 A, 10 kAIC, Single-pole, 120 V, GFEP, Common, #14-4 AWG, Ground fault circuit interrupter, GFI

### General specifications

<b>PRODUCT NAME</b>	Eaton BR GFCI circuit breaker
<b>CATALOG NUMBER</b>	GFEP120
<b>UPC</b>	786676382052
<b>PRODUCT LENGTH/DEPTH</b>	3 in
<b>PRODUCT HEIGHT</b>	1.25 in
<b>PRODUCT WIDTH</b>	4.75 in
<b>PRODUCT WEIGHT</b>	0.45 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 489
<b>CATALOG NOTES</b>	Meets Federal Spec Classification W-C375



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Industrial ground fault thermal-magnetic equipment protector
<b>AMPERAGE RATING</b>	20 A
<b>VOLTAGE RATING</b>	120 V
<b>TRIP TYPE</b>	Common
<b>CIRCUIT PROTECTION</b>	Ground fault circuit interrupter
<b>INDICATORS</b>	GFI
<b>INTERRUPT RATING</b>	10 kAIC
<b>MAIN CIRCUIT BREAKER</b>	GFEP
<b>WIRE SIZE</b>	#14-4 AWG
<b>NUMBER OF POLES</b>	Single-pole

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - GFEP120</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

