

## Features

- Automatic ON operation
- Automatic Voltage Detection eliminates the need for specialized wiring
- Zero Arc Point Switching Minimizes relay contact
- Easily mounts inside or outside a junction box or inside a fluorescent fixture ballast cavity.
- Plenum rated

## Ordering Information

Description	Device Color	UPC Number	Catalog Number
Automatic-on operation, 120/277V AC, 50/60Hz	Black	783585181004	CU300A

## Listings

cULus listed to UL 916  
UL2043 plenum rated per NEC® 2014 300.22(C)(3)  
ASHRAE 90.1 compliant

## Specifications

Housing	Flame retardant UL 94-5VA thermoplastic
Dimensions	3.69"L x 2.33"W x 1.36"H


## Performance

### Electrical

AT Sensor/AAR Capacity	1 to 4 combined
Load Capacity	Incandescent - 0 to 1800 watts, 120V Ballast- 0 to 2400 watts, 277V Ballast- 0 to 5540 watts
Power Output	24V DC, 150mA
Power Supply	120-277V AC, 50/60Hz

### Environmental

Operating Temperature	32°F to 104°F (0°C to 40°C); 0% to 90% non condensing relative humidity
Storage Temperature	-20°F to 150°F (-29°C to 65°C); 0% to 90% non condensing relative humidity



## Complementary Products

Add-A-Relay                      AAR

## Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

## Features

- Automatic ON operation
- Automatic Voltage Detection eliminates the need for specialized wiring
- Zero Arc Point Switching Minimizes relay contact
- Easily mounts inside or outside a junction box or inside a fluorescent fixture ballast cavity.
- Plenum rated

## Ordering Information

Description	Device Color	UPC Number	Catalog Number
Automatic-on operation, 120/277V AC, 50/60Hz	Black	783585181004	CU300A

## Listings

cULus listed to UL 916  
UL2043 plenum rated per NEC® 2014 300.22(C)(3)  
ASHRAE 90.1 compliant

## Specifications

Housing	Flame retardant UL 94-5VA thermoplastic
Dimensions	3.69"L x 2.33"W x 1.36"H


## Performance

### Electrical

AT Sensor/AAR Capacity	1 to 4 combined
Load Capacity	Incandescent - 0 to 1800 watts, 120V Ballast- 0 to 2400 watts, 277V Ballast- 0 to 5540 watts
Power Output	24V DC, 150mA
Power Supply	120-277V AC, 50/60Hz

### Environmental

Operating Temperature	32°F to 104°F (0°C to 40°C); 0% to 90% non condensing relative humidity
Storage Temperature	-20°F to 150°F (-29°C to 65°C); 0% to 90% non condensing relative humidity



## Complementary Products

Add-A-Relay                      AAR

## Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions