

Power Protection Devices, Receptacle, Self Test, GFCI, TRWR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White Almond

By Hubbell Wiring Device-Kellems
Catalog # [GFRTW20W](#)

Power Protection Devices, Receptacle, Self Test, GFCI, TRWR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White Almond



Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired
- Single LED status indicator - green indicates power, red indicates a trip, flashing red indicates end of life

General

Catalog Number	GFRTW20W
Color	White
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	<ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Zinc plated steel• Power Contacts - Brass
Style	Standard

Type

Tamper-Resistant, Weather Resistant

UPC

883778999413

Electrical Ratings

Current / Amperage Rating 20 A
Voltage Rating Description 125 V

Certifications And Compliance

Industry Standard(s) Meets All NEC® Requirements
Nema Rating 5-20R

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - WDK K-7 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - M-14627 AutoCAD Drawing](#)
[Installation Manuals - PD2987](#)
[Literature - Commercial GFCI Receptacles](#)
[Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles](#)
[Sales Drawings - M14627](#)
[Specifications - WIRING_GFRTW20W_spec](#)