

GGC

Electronic/Glass Fuses

MIDGET, PC MOUNT & MINIATURE FUSES

FEATURES/BENEFITS

- Glass body
- Fast-acting
- 1/4" x 1-1/4"

APPROVALS/STANDARDS

- 1/2A through 10A, 250VAC, UL Listed and CSA Certified
- 12A and 15A, 125VAC, UL Listed and CSA Certified
- 20A through 30A, 32VAC



STANDARD FUSE AMPERE RATINGS

Catalog Number	Ampere Rating	Volts	I.R.
GGC1/2	1/2A	250V	1
GGC3/4	3/4A	250V	1
GGC1	1A	250V	1
GGC1-1/4	1-1/4A	250V	1
GGC1-3/4	1-3/4A	250V	1
GGC1-6/10	1-6/10A	250V	1
GGC2	2A	250V	1
GGC2-1/2	2-1/2A	250V	1
GGC3	3A	250V	1
GGC4	4A	250V	1
GGC5	5A	250V	1
GGC6	6A	250V	1
GGC7	7A	250V	1
GGC8	8A	250V	1
GGC10	10A	250V	1
GGC12	12A	125V	2
GGC15	15A	125V	2
GGC20	20A	32V	3
GGC25	25A	32V	3
GGC30	30A	32V	3

1. 250VAC @ 200A I.R./125VAC @ 10kA I.R.
2. 125VAC @ 10kA I.R.
3. 32VAC @ 1000A I.R.

GGC

Electronic/Glass Fuses

MIDGET, PC MOUNT & MINIATURE FUSES

FEATURES/BENEFITS

- Glass body
- Fast-acting
- 1/4" x 1-1/4"

APPROVALS/STANDARDS

- 1/2A through 10A, 250VAC, UL Listed and CSA Certified
- 12A and 15A, 125VAC, UL Listed and CSA Certified
- 20A through 30A, 32VAC



STANDARD FUSE AMPERE RATINGS

Catalog Number	Ampere Rating	Volts	I.R.
GGC1/2	1/2A	250V	1
GGC3/4	3/4A	250V	1
GGC1	1A	250V	1
GGC1-1/4	1-1/4A	250V	1
GGC1-3/4	1-3/4A	250V	1
GGC1-6/10	1-6/10A	250V	1
GGC2	2A	250V	1
GGC2-1/2	2-1/2A	250V	1
GGC3	3A	250V	1
GGC4	4A	250V	1
GGC5	5A	250V	1
GGC6	6A	250V	1
GGC7	7A	250V	1
GGC8	8A	250V	1
GGC10	10A	250V	1
GGC12	12A	125V	2
GGC15	15A	125V	2
GGC20	20A	32V	3
GGC25	25A	32V	3
GGC30	30A	32V	3

1. 250VAC @ 200A I.R./125VAC @ 10kA I.R.
2. 125VAC @ 10kA I.R.
3. 32VAC @ 1000A I.R.

© 2025 Mersen. All rights reserved. Mersen reserves the right to change, update, or correct, without notice, any information contained in this datasheet.