



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GHB2020 Type GHB BRKR 2P 20A 277/480VAC Max 125/250VDC Max *Eaton Corp*

| | |
|------------------|---|
| Catalog Number | GHB2020 |
| Manufacturer | Eaton Corp |
| Description | Molded Case Circuit Breaker, 20 A, Non-Interchangeable Thermal Magnetic Tripping Mechanism, Bolt-On, 277/480 V Ac;125/250 V DC, G-Frame Frame, 50/60 HZ, 2.8 In Overall Height, 4.7 In Overall Length, 2.1 In Overall Width |
| Weight per unit | 0.9500 (lbs/each) |
| Product Category | 2 Pole |

Features

| | |
|----------------|-----------------------------------|
| Current Rating | 20 A |
| dimensions | 2.6300 IN X 2.0000 IN X 4.0000 IN |
| frame | G |
| media | Yes |
| Poles | 2 |

Descriptions

| | |
|------------------------|--|
| Description | TYPE GHB BRKR 2P 20A 277/480VAC MAX 125/250VDC MAX |
| extra long description | ETN GHB2020 GHB CB 2P 20A 277/480VA |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Viton(R) |
| GTIN | 00786679911204 |
| UPC | 786679911204 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS |
| Type | Molded case circuit breaker |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.95 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other |
| standard | UL Listed,Federal Specifications Classification W-C375B |