



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GHB3070 Type GHB BRKR 3P 70A 277/480VAC Max 125/250VDC Max *Eaton Corp*

Catalog Number	GHB3070
Manufacturer	Eaton Corp
Description	Molded Case Circuit Breaker, 70 A, Non-Interchangeable Thermal Magnetic Tripping Mechanism, 277/480 V Ac;125/250 V DC, G-Frame Frame, 50/60 HZ, 4 In Overall Height, 3.8 In Overall Width
Weight per unit	1.8 (lbs/each)
Product Category	3 Pole

Features

dimensions	2.6300 IN X 3.0000 IN X 4.0000 IN
frame	G
media	Yes
Poles	3

Descriptions

Description	TYPE GHB BRKR 3P 70A 277/480VAC MAX 125/250VDC MAX
extra long description	ETN GHB3070 GHB CB 3P 70A 277/480VA

Manufacturer Information

GTIN	00786679911310
UPC	786679911310

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Molded case circuit breaker

Packaging

Carton	1
Weight Per each	1.75

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
standard	UL Listed,Federal Specifications Classification W-C375B